DTK-SL "Snap-Lite" Series

66 Block Quick-Connect Surge Protectors





Product Features

- Quick connect module no bridge clips required!
- Each Snap-Lite protects one pair
- Field-replaceable modules
- Self-resetting fuse on models with "A" suffix
- Models available for both current-limited and standard lines

Applications

Voice/Data Professionals

Note

• Each 66 Block requires one ground bar: **DTK-SIGB**



DITEK's DTK-SL Series guick-connect line protectors are designed specifically for Voice/Data professionals. Snap-Lite provides both voltage and current limiting in addition to surge protection. The unique multi-function diagnostic LED shows protection status, line continuity and line usage. Available in four different voltages, there is a Snap-Lite for virtually any analog 66 block application.

Technical Specifications				
DTK-	SL30	SL50	SL95	SL130
Service Voltage:	30V	50V	95V	130V
MCOV:	38VDC	66VDC	127VDC	175VDC
Clamping Voltage:	47V	82V	150V	204V
Protection Modes:	Tip-Ground, Ring-Ground			
Surge Current Rating:	1,000 Amps per pair	5,000 Amps per pair	4,000 Amps per pair	4,000 Amps per pair
Max Continuous Current:	"-A" models 150mA "-B" models 2A			

Mechanical Characteristics

Base Connection Method:	Press-to-Fit connection to 66 Block		
Housing:	High Impact Plastic		
Operating Temperature:	-40°F - 158°F (-40°C - 70°C)		
Maximum Humidity:	95% non-condensing		
Dimensions:	.3.24"L x .38"W x 1.56"H (82.3mm x 9.6mm x 39.6mm)		
Weight:	.5oz (14g)		

Quality, Standards & Approval

Agency Approvals:	"-A" models UL497A "-B" models UL497B
Warranty:	Ten Year Limited Warranty

Every precaution has been taken to ensure that this literature is accurate and complete. DITEK Corporation assumes no responsibility and disclaims all liability for damages resulting from the use of this information or for any errors or omissions.

Doc. Number: SPS-100055-001 Rev 4 08/16





