



760201152 | 360-iP-1100-E-1U-BLANK

SYSTIMAX 360™ iPatch® 1100 Evolve Panel, 24 port without modules

Dimensions

Depth	206.50 mm 8.13 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Height	44.45 mm 1.75 in
Width	482.60 mm 19.00 in

Electrical Specifications

Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	iPatch® enabled
Total Ports, quantity	24
Cable Type	U/UTP (unshielded)
Product Type	Panel
Color	Silver
Package Quantity	1
Rack Units	1

Mechanical Specifications

Plug Insertion Life, minimum	750 times
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification