



760193813 | 360-iP-INSTA-LC-4TS

**SYSTIMAX 360™ iPatch® G2 Fiber Shelf with InstaPATCH 360 TeraSPEED Modules**

## Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1   OS2)
Material Type	ABS   Polycarbonate

## Dimensions

Depth	355.60 mm   14.00 in
Height	44.45 mm   1.75 in
Width	482.60 mm   19.00 in
Weight	2.95 kg   6.50 lb

## Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel   CE   CSA   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

## General Specifications

Brand	SYSTIMAX 360™   SYSTIMAX®   iPatch®
Intelligence Type	iPatch® enabled
Product Type	Shelf, preterminated
Shelf Movement	Sliding
Color	Black
Interface	LC
Package Quantity	1
Total Ports, quantity	24

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

