Product Specifications



760201194 | 360-iP-MFTP-E-1U-BLANK

SYSTIMAX 360™ iPatch® FTP Evolve Modular Panel, 24 port without modules

Dimensions

 Depth
 206.50 mm | 8.13 in

 Diameter Over Dielectric, maximum
 1.168 mm | 0.046 in

 Height
 44.45 mm | 1.75 in

 Width
 482.60 mm | 19.00 in

Electrical Specifications

Current Rating 1.5 A @ 20 $^{\circ}$ C 1.5 A @ 68 $^{\circ}$ F

Dielectric Withstand Voltage, RMS, conductive surface 1500 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Environmental Specifications

Operating Temperature $-10 \, ^{\circ}\text{C}$ to $+60 \, ^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Safety Standard CUL | UL

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type iPatch® enabled

Total Ports, quantity 24
Product Type Panel
Color Silver
Package Quantity 1
Rack Units 1

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Wiring T568A | T568B

Regulatory Compliance/Certifications

Agency Classification

RoHS 2011/65/EU ISO 9001:2008