



CCRRD | IP6A-12LUTP-1100E-1100E

InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 12 links

Ordering Details

Complete Part Number	Complete Description Code	Interface Orientation, connector A	Interface Orientation, connector B	Bundling Style	Information Outlet Color	Cable Jacket Color	Length
CCRRD-53SA08F150	IP6A-12LUTP-1100E-1100E-LSF-RSF-SG-WH-150F	5 - Left series flat	3 - Right series flat	S - Sleeving	0 - Not applicable	8 - White	150 ft

↳ InstaPATCH® Cu GigaSPEED X10D® U/UTP LSZH Preterminated Copper Cable, 360 1100 Evolve module to 360 1100 Evolve module, 12 links, left series flat to right series flat, sleeving, white jacket, 150 ft

Dimensions

Cord Length, minimum	5 m 17 ft
Cord Length, maximum	90 m 295 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Brand	GigaSPEED X10D® InstaPATCH® Cu SYSTIMAX®
Cable Type	U/UTP (unshielded)
Interface, connector A	360 1100 Evolve module
Interface, connector B	360 1100 Evolve module
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard

Mechanical Specifications

Link Count	12
Conductor Type	Solid

CCRRD | IP6A-12LUTP-1100E-1100E

Wiring T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

- 760151183 | 360-IPR-1100-GS6-DM6 — SYSTIMAX 360™ GigaSPEED X10D® 1100GS6 Evolve Category 6A U/UTP Distribution Module, 6 port
- 3091B 4/23 (Product Component—not orderable) — GigaSPEED X10D® 3091B ETL Verified Category 6A U/UTP Cable, 4 pair count,