

FAWSCUC0C

TeraSPEED® SC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 12-fiber Kit, Blue - Aqua (1-12)

Ordering Details

Part Number	Jacket Color	Breakout Length	Cable Glands	Pulling Grips, qty	Length
FAWSCUC0C-XXF005	Color is not configurable	N/A	No glands	0	5 ft

↳ TeraSPEED® SC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, 12-fiber Kit, Blue - Aqua (1-12), 5 ft

Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Total Fibers, quantity	12

Dimensions

Cord Length, maximum	23 ft 7 m
Cord Length, minimum	2 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	Pigtail kit
Interface, connector A	SC
Interface Feature, connector A	Standard
Color, connector A	Blue
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

FAWSCUCOC

X-TB-8W (Product Component—not orderable) — 900µm Tight Buffered Fiber

- CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber

460125842 (Product Component—not orderable) — Behind The Wall Pre-Radiused SC Connector for 0.9 mm Fiber, single-mode