

FAXLCUC01

LazrSPEED® 550 LC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer

Ordering Details

Part Number	Jacket Color	Breakout Length	Cable Glands	Pulling Grips, qty	Length
FAXLCUC01-MXF007	Aqua	N/A	No glands	0	7 ft

 LazrSPEED® 550 LC to Unconnectorized, Fiber Pigtail, 0.9 mm Tight Buffer, aqua jacket, 7 ft

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber (OM4)
Total Fibers, quantity	1

Dimensions

Cord Length, maximum	23 ft 7 m
Cord Length, minimum	2 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Plenum
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Construction Type	Pigtail, unjacketed
Interface, connector A	LC
Interface Feature, connector A	Standard
Color, connector A	Beige
Interface, connector B	Unterminated

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 ° 1.00 lb @ 90 °
-----------------------------------	---------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

X-TB-5K (Product Component—not orderable) — 900µm Tight Buffered Fiber

FAXLCUC01

- CS-5K-TB (Product Component—not orderable) — LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

460125271 (Product Component—not orderable) — Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode