


FJWMPMPAF

TeraSPEED® MPO (female) to MPO (female), InstaPATCH® 360 Pre-terminated Trunk Cable, 24-Fiber, LSZH

Ordering Details

Part Number	Jacket Color	Breakout Length	Cable Glands	Pulling Grips, qty	Length
FJWMPMPAF-JAF050	Yellow	Standard	Not included	0	50 ft

 TeraSPEED® MPO (female) to MPO (female), InstaPATCH® 360 Pre-terminated Trunk Cable, 24-Fiber, LSZH, yellow jacket, standard breakout without gland, 50 ft

Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Total Fibers, quantity	24
Fibers per Subunit, quantity	12
Furcation Color	Yellow

Dimensions

Breakout Length	33 in
Cord Length, maximum	999 ft 999 m
Cord Length, minimum	10 ft 3 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Brand	InstaPATCH® 360
Color, connector A	Green
Color, connector B	Green
Construction Type	InstaPATCH® 360 trunk/extension/cross-connect, indoor
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Interface, connector A	MPO Female
Interface, connector B	MPO Female
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

FJVM/MPMPAF

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system



Included Products

N-024-MP-8W-F12 (Product Component—not orderable) — Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 fiber with 12 fiber subunits

- CS-8W-MP (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber

860366137 (Product Component—not orderable) — TeraSPEED® MPO Female 12 Fiber Connector, green