

FNWLCLCAF

TeraSPEED® LC to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, LSZH

Ordering Details

Part Number	Jacket Color	Breakout Length	Cable Glands	Pulling Grips, qty	Length
FNWLCLCAF-JFF045	Yellow	24 in	Included	0	45 ft

↳ TeraSPEED® LC to LC, InstaPATCH® 360 Ruggedized Fanout Cable, 24-Fiber, LSZH, yellow jacket, 24 in breakout with gland, 45 ft

Construction Materials

Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D, G.657.A1 or G.652.D, G.657.A1 OS2)
Total Fibers, quantity	24
Fibers per Subunit, quantity	12
Furcation Color	Yellow

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	3 m 8 ft
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

General Specifications

Brand	InstaPATCH® 360
Color, connector A	Blue
Color, connector B	Blue
Construction Type	InstaPATCH® 360 ruggedized fanout, indoor
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Interface, connector A	LC
Interface, connector B	LC
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

N-024-MP-8W-F12 (Product Component—not orderable) — Low Smoke Zero Halogen Riser MPO Trunk Cable, 24 fiber with 12 fiber subunits

- CS-8W-MP (Product Component—not orderable) — TeraSPEED® OS2 Singlemode Fiber

460125206 (Product Component—not orderable) — Pre-Radiused LC Connector duplex for 1.6 mm Fiber, single-mode