

CA1G772-58 | G10FP-HGS620MS(IV)-L-WH

GigaSPEED X10D® G10FP to M-series HGS620 on 3295 Solid Low Smoke Zero Halogen Cordage F/UTP Zone Extension Cord, white jacket, ivory information outlet

Ordering Details

Complete Part Number	Complete Description Code	Cord Length
CA1G772-58F050	G10FP-HGS620MS(IV)-L-WH-50FT	50 ft

Dimensions

Cord Length, maximum	100 m 300 ft
Cord Length, minimum	1 m 3 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Cable Type	F/UTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	Information outlet
Jacket Color	White
Brand	GigaSPEED X10D® SYSTIMAX 360™ SYSTIMAX®
Information Outlet Color	Ivory
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package Quantity	1
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy Polycarbonate
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2008

Classification

Compliant

Compliant



Included Products

860382605 | 3295A WH 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, variable length, reel

3295A 4/24 (Product Component—not orderable) — GigaSPEED X10D® 3295A Category 6A F/UTP Cable, low smoke zero halogen, 4 pair count