



## IQZ1QPQPV4-F

**InstaPATCH® QUATTRO MC Male to MC Male Category 6A U/UTP Bundled Trunk Cable, 4-port, low smoke zero halogen, white**

### Ordering Details

<b>Complete Part Number</b>	<b>Cord Length</b>
IQZ1QPQPV4-FF022	22 ft

### Dimensions

Cord Length, maximum	90 m   295 ft
Cord Length, minimum	3 m   10 ft

### Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	1000 V

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL   ETL

### General Specifications

Construction Type	Bundled
Interface, connector A	MC Male
Interface, connector B	MC Male
Brand	InstaPATCH® QUATTRO
Cable Type	U/UTP (unshielded)
Information Outlet Color	Silver
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	White
Package Quantity	1
Pairs, quantity	16
Total Ports, quantity	4

### Mechanical Specifications

Conductor Type	Solid
Material Type	Copper alloy   Polycarbonate   Zinc

IQZ1QPQPV4-F

Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, connector A, minimum	100 times
Plug Insertion Life, connector B, minimum	100 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2008

### Classification

Compliant  
Designed, manufactured and/or distributed under this quality management system

