



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT P/N | DESCRIPTION                      | CABLE DIAMETER             | PACKAGING               | APPROXIMATE WEIGHT (CABLE ONLY) | JACKET TYPE |
|-------------|----------------------------------|----------------------------|-------------------------|---------------------------------|-------------|
| PFL6004**-G | CATEGORY 6 F/UTP<br>4-PAIR 23AWG | 7.5MM (0.296IN)<br>NOMINAL | 305 M (1000 FT)<br>REEL | 15 KG/305 M<br>(32 LB/1000 FT)  | LSZH        |



NOTES:

1. \*\* - INDICATES CABLE JACKET COLOR  
SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER  
SUFFIXES INDICATING JACKET COLOR.
2. DIMENSIONS IN BRACKETS ARE IMPERIAL.
3. COLOR CODES:  
PAIR 1 WHITE/BLUE - BLUE  
2 WHITE/ORANGE - ORANGE  
3 WHITE/GREEN - GREEN  
4 WHITE/BROWN - BROWN
4. DURING INSTALLATION, SEPARATE INDIVIDUAL PAIRS.  
START WITH THE OUTSIDE PAIRS AND MOVE INWARD TO  
EASE PAIR TERMINATION.

|                                                                                       |                    |                          |   |
|---------------------------------------------------------------------------------------|--------------------|--------------------------|---|
| MODEL FILENAME                                                                        | MO1948BT/00        | SIZE                     | A |
| DRAWING FILENAME                                                                      | MO1948BT_DC115/00A |                          |   |
| TX6000 CATEGORY 6 4-PAIR<br>F/UTP CABLE CUSTOMER DRAWING                              |                    |                          |   |
|  |                    | I.I. NUMBER              |   |
| PANDUIT <sup>TM</sup> CORP.<br>TINLEY PARK, ILL 60477                                 |                    | PRODUCT SPEC/ PKG SPEC   |   |
|  |                    | ASSY METHOD/ TEST METHOD |   |
| THIRD ANGLE<br>PROJECTION                                                             |                    | SCALE<br>NONE            |   |
| DRAWN BY<br>BJN                                                                       |                    | REVIEW DRAWING NUMBERS   |   |
| DATE<br>11/6/09                                                                       |                    | PART NO.<br>SEE TABLE    |   |
| CHK'D<br>GEF                                                                          |                    | DRAWING NO.<br>01948-115 |   |

|     |         |     |     |                        |           |     |      |     |     |
|-----|---------|-----|-----|------------------------|-----------|-----|------|-----|-----|
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
|     |         |     |     |                        |           |     |      |     |     |
| R   | 11-6-09 | BJN | GEF | RELEASED TO PRODUCTION | 01948-115 | GAZ |      |     |     |
| REV | DATE    | BY  | CHK | DESCRIPTION            | ECN       | R   | CUST | SUP | OTH |