


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
1. TX5e CATEGORY 5e UTP LSZH PATCH CORD
 2. 100% PERFORMANCE TESTED TO CAT5e PATCH CORD LIMITS.
 3. TERMINATED WITH (8 POSITION) MODULAR PLUGS AT BOTH ENDS PER T568A.
 4. CONSTRUCTED WITH 24AWG STRANDED CAT5e UTP LSZH PATCH CABLE
 5. MATERIALS:
PLUG: POLYCARBONATE
 6. NOMINAL CABLE DIAMETER IS 0.215 IN (5.46MM).
 7. OPERATING TEMPERATURE: -10°C TO 60°C.
 8. STORAGE TEMPERATURE: -40°C TO 70°C.
 9. UL LISTED, FILE NUMBER E12986

T568A WIRING SCHEME

| PLUG POSITION | CABLE WIRE |
|---------------|--------------|
| 1 | WHITE/GREEN |
| 2 | GREEN |
| 3 | WHITE/ORANGE |
| 4 | BLUE |
| 5 | WHITE/BLUE |
| 6 | ORANGE |
| 7 | WHITE BROWN |
| 8 | BROWN |

| CABLE COLORS | ** = COLOR |
|--------------|------------|
| OFF-WHITE | BLANK |
| BLUE | BU |
| RED | RD |
| GREEN | GR |
| ORANGE | OR |

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

| | | | |
|---|---------|-----------------------------|-------|
| PART NUMBER | | UTPCHLXX**Y | |
| TITLE | | TX5e UTP PATCH CORDS (LSZH) | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M02479MJ/07 | |
| DATASET FILE NAME | | M02479MJ_DC323/07D | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | | MATERIAL: | |
| .x ± .xxx ± .010 (.3) | | SEE NOTES | |
| .xx ± .03 (.8) ANGLES ± | | DRAWING NUMBER: | |
| THIRD ANGLE PROJECTION | | 02479-323 | |
| DRAWN BY | DATE | CHK | SCALE |
| NER | 3-23-06 | WJC | NONE |
| SHT 1 OF 2 | | | SIZE |
| | | | A |



| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|--------|-----|-----|-----|--|-----------|
| 3 | 4-9-14 | BJN | JSP | EJH | REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY | 02479-323 |

D10100DA/14

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX5e UTP LSZH PATCH CORDS

| PANDUIT PART NUMBER | MIN. CABLE LENGTH |
|---------------------|-------------------|
| UTPCHL0.5M**Y | 0.5 m |
| UTPCHL1M**Y | 1 m |
| UTPCHL1.5M**Y | 1.5 m |
| UTPCHL2M**Y | 2 m |
| UTPCHL2.5M**Y | 2.5 m |
| UTPCHL3M**Y | 3 m |
| UTPCHL3.5M**Y | 3.5 m |
| UTPCHL4M**Y | 4 m |
| UTPCHL4.5M**Y | 4.5 m |
| UTPCHL5M**Y | 5 m |
| UTPCHL6M**Y | 6 m |
| UTPCHL7M**Y | 7 m |
| UTPCHL8M**Y | 8 m |
| UTPCHL9M**Y | 9 m |
| UTPCHL10M**Y | 10 m |
| UTPCHL15M**Y | 15 m |
| UTPCHL20M**Y | 20 m |
| UTPCHL25M**Y | 25 m |
| UTPCHL30M**Y | 30 m |
| UTPCHL35M**Y | 35 m |
| UTPCHL40M**Y | 40 m |

| | | | |
|---|---|---|-------|
| PART NUMBER | | UTPCHLXX**Y | |
| TITLE | | | |
| TX5e UTP PATCH CORDS (LSZH) | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M02479MJ/07 | |
| DATASET FILE NAME | | M02479MJ_DC323/07D | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) | |  | |
| .x ± .xxx ± .010 (.3) .xx ± .03 (.8) ANGLES ± | | | |
| DRAWING NUMBER: | | 02479-323 | |
| THIRD ANGLE PROJECTION |  | | |
| DRAWN BY | DATE | CHK | SCALE |
| NER | 3-23-06 | WJC | NONE |
| SHT 2 OF 2 | | | SIZE |
| | | | A |

| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN |
|-----|--------|-----|-----|-----|----------------------------------|-----------|
| 3 | 4-9-14 | BJN | JSP | EJH | SEE SHEET 1 FOR REVISION HISTORY | 02479-323 |

D10100DA/14