




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES :

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.




TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS - MULTIMODE	BEND RADIUS	
3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	INSTALLATION	LONG TERM
	11.6cm [4.6"]	5.8cm [2.3"]
MAXIMUM LOSS - SINGLEMODE	TENSILE LOAD	
.75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	INSTALLATION	LONG TERM
	660 N [150 lbf]	200 N [45 lbf]
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-10° C TO +60° C 14° F TO +140° F	-20° C TO +70° C -4° F TO +158° F	-40° C TO +70° C -40° F TO +158° F

											TITLE 8, 12 FIBER INDOOR/OUTDOOR CABLE WITH 900um TIGHT BUFFER CUSTOMER DRAWING		
											ITEM REVISION NAME M02055KC/00		
											DATASET FILE NAME M02055KC_DC/00A		
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±		
											 THIRD ANGLE PROJECTION		PART NO. SEE TABLE
											DRAWING NUMBER: M02055KC-DC		
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055KC-DC							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-13-14	CHK WMA	SCALE NONE	SHT 1 OF 2		SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	FIBER TYPE	FIBER COUNT	JACKET FLAME RATING
FLKR508	MULTIMODE 50/125 OM2	8	OFNR
FLKL508			LSZH
FLKR512		12	OFNR
FLKL512			LSZH
FLKR608	MULTIMODE 62.5/125 OM1	8	OFNR
FLKL608			LSZH
FLKR612		12	OFNR
FLKL612			LSZH
FLKRX08	MULTIMODE 50/125 OM3	8	OFNR
FLKLX08			LSZH
FLKRX12		12	OFNR
FLKLX12			LSZH
FLKRZ08	MULTIMODE 50/125 OM4	8	OFNR
FLKLZ08			LSZH
FLKRZ12		12	OFNR
FLKLZ12			LSZH
FLKR908	SINGLEMODE 9/125	8	OFNR
FLKL908			LSZH
FLKR912		12	OFNR
FLKL912			LSZH

							TITLE 8, 12 FIBER INDOOR/OUTDOOR CABLE WITH 900 μ m TIGHT BUFFER					
							CUSTOMER DRAWING					
							ITEM REVISION NAME M02055KC/00		PANDUIT			
							DATASET FILE NAME M02055KC_DC/00A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X \pm .03 (0.8) .XXX \pm .010 (0.3) .XX \pm .03 (0.8) ANGLES \pm		PART NO. SEE TABLE			
							THIRD ANGLE PROJECTION 		DRAWING NUMBER: M02055KC-DC			
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION	M02055KC-DC	DRAWN BY SAT	DATE 02-13-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN						