


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


FIBER POSITION
X X 3 4 5 6 7 8 9 10 X X



MPO KEY
LEFT



5.0
[128]



LC CONNECTOR
LATCH DOWN

4.2
[106]

.8
[21]


FIBER POSITION X X 4 3 6 5 8 7 10 9 X X

METHOD A 8F - CASSETTE (AF)													
MPO END / LC END	FIBER POSITION FROM MPO END TO LC END												
MPO	X	X	3	4	5	6	7	8	9	10	X	X	
LC	N/A	N/A	4	3	6	5	8	7	10	9	N/A	N/A	

PANDUIT PART NUMBER	FIBER TYPE	PERFORMANCE LEVEL	ADAPTER COLOR (SPLIT SLEEVE)
FQXN-08-10AF	OM3	STANDARD LOSS	AQUA (ZIRCONIA)
FQX0-08-10AF	OM3	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQZN-08-10AF	OM4	STANDARD LOSS	AQUA (ZIRCONIA)
FQZ0-08-10AF	OM4	OPTIMIZED LOSS	AQUA (ZIRCONIA)
FQSA-08-10AF	OM4+ (SIG CORE)	ULTRA LOW LOSS	AQUA (ZIRCONIA)
FQ9N-08-10AF	OS1/OS2	STANDARD LOSS	BLUE (ZIRCONIA)

NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
A. MODULE MATERIAL: PLASTIC
B. ADAPTER: COMPOSITE PLASTIC
- CASSETTE MODULE WEIGHT:
2.4oz [69.0g]
- DIMENSIONS IN BRACKETS ARE METRIC
- METHOD A CASSETTES COMPLY WITH ANSI/TIA-568-C.O.
SEE ANSI/TIA-568-C.O. FOR POLARITY DETAILS AND EXAMPLE OF A BASIC LINK.



PART NUMBER		FQ**-08-10AF	
TITLE			
QUICKNET SFQ SERIES CASSETTE, 8 FIBER DUPLEX LC TO MPO CASSETTE METHOD A, PAIR FLIPPED			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02947ZC/04	
DATASET FILE NAME		M02947ZC_DC/04A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ±		.XXX ±	
.XX ±		ANGLES ±	
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
02947-32		02947-32	
DRAWN BY	DATE	CHK	SCALE
EFK	9-19-09	WMA	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	11/19/15	JSP	WJM	RAR	B. CORRECTED LOCATION OF LC CONNECTORS IN CASSETTE. A. UPDATED DRAWING TITLE BLOCK.	02947-32