


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT PART NUMBER | LENGTH (TIP TO TIP) |
|------------------------|------------------------|
| FVFLPCY | 1 METER [3.28 FEET] |

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. CONSTRUCTED WITH 50/125 MICRON MULTIMODE CABLE AND A PHOSPHOROUS BRONZE SPLIT SLEEVE.
3. EXTRA SPLIT SLEEVES ARE PROVIDED AS REPLACEMENTS.
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTIONS OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

| | | | |
|--|----------|-------------------|-------|
| PART NUMBER | | FVFLPCY | |
| TITLE | | | |
| V.F.K. PATCH CORD | | | |
| CUSTOMER DRAWING | | | |
| ITEM REVISION NAME | | M01686AF/02 | |
| DATASET FILE NAME | | M01686AF_DC-Y_02C | |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] | | | |
| .X ± .XX ± | | | |
| .XXX ± ANGLES ± | | MATERIAL: | |
| | | DRAWING NUMBER: | |
| THIRD ANGLE PROJECTION | | 01686-06 | |
| DRAWN BY | DATE | CHK | SCALE |
| EFK | 06-18-03 | MMW | NONE |
| SHT 1 OF 1 | | | SIZE |
| | | | A |

| 2 | 8/25/15 | JSP | WJM | RWB | A. UPDATED DRAWING TITLE BLOCK. | 0168-06 | |
|-----|---------|-----|-----|-----|---------------------------------|---------|--|
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN | |