




- NOTES:
1. SEE SHEET 2 FOR PART NUMBERS.
 2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 3. FLAME RATING:
 - A. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
 - B. PLENUM RATED CABLE ASSEMBLIES MEET NFPA 262.
 4. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 5. CONTACT PANDUIT FOR PRODUCT PERFORMANCE.
 6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 7. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



							TITLE					
							12 FIBER MPO TO LC SMALL DIAMETER TRUNK CABLE WITH PULLING EYE					
							CUSTOMER DRAWING					
							ITEM REVISION NAME		12F178BN/00			
							DATASET FILE NAME		12F178BN_DC/00A			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
							.X ± .XXX ± .010 [0.3]					
							.XX ± .03 [0.8] ANGLES ±					
00	09-18-13	SAT	WMA		RELEASED TO PRODUCTION	12F178BN-DC	 THIRD ANGLE PROJECTION				DRAWING NUMBER: 12F178BN-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE B
							SAT	09-18-13	WMA	NONE		

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
F		T	Y			E	L	2						

FIBER TYPE

9 - OS1/OS2
X - OM3
Z - OM4

FLAME RATING

L - LSZH
P - OFNP

CONNECTOR TYPE

5 - MTP (FEMALE)
6 - MTP (MALE)
7 - PANMPO (FEMALE)
8 - PANMPO (MALE)

PERFORMANCE/POLARITY

S - STANDARD PERFORMANCE (SEE NOTE 8)
O - OPTIMIZED PERFORMANCE (SEE NOTE 8)

PULLING EYE

A - PULLING EYE (MTP/PANMPO END)
N - NO PULLING EYE



UNIT OF MEASURE

M - METERS
F - FEET

LENGTH

B

A

							TITLE		12 FIBER MPO TO LC SMALL DIAMETER TRUNK CABLE WITH PULLING EYE				
									CUSTOMER DRAWING				
							ITEM REVISION NAME		12F178BN/00				
							DATASET FILE NAME		12F178BN_DC/00A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:				
							.X ± .XXX ± .010 [0.3] .XX ± .03 [0.8] ANGLES ±						
									DRAWING NUMBER: 12F178BN-DC				
							THIRD ANGLE PROJECTION						
00	09-18-13	SAT	WMA		RELEASED TO PRODUCTION		12F178BN-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 2		SIZE
							SAT	09-18-13	WMA	NONE			B

2



1