



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ITEM NO.	PART NO.	DESCRIPTION	QTY.
1	ZAPDUMOD-04	LCD PANEL - MONITOR BOARD	1
2	LBSINETICA-03	UNITE LCD LABEL	1
3	COMMANDO PLUG	32 AMP, 3 PIN, MALE	1
4	CABLE - 3 METERS	3 METER LENGTH	1
5	C13	10 AMP IEC	22
6	C19	16 AMP IEC	3
7	MAX 10 AMP FUSE HOLDER	FITTED WITH 10 AMP FUSE	1
8	NEON	RED NEON	25

DEFAULT OUTLETS STATE FOR CONTROLLABLE PDU	ON
INTERNAL POWER SUPPLY	NO
COMMUNICATION MODE	RS485



R	05/27/14	PJST	JPMC	TSB	RELEASED TO PRODUCTION	13A095EA-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE						
32AMP, SINGLE PHASE, VERTICAL, TOP FED PDU, 32 AMP 3 PIN COMMANDO 3m STANDARD CABLE, 21x LOCKING C13 INDIVIDUAL NEON, 3x LOCKING C19 INDIVIDUAL NEON, FITTED WITH ALWAYS ON C13 INDIVIDUAL FUSE AND NEON, PER OUTLET MONITOR AND CONTROL. CUSTOMER DRAWING						
ITEM REVISION NAME						
13A095EA/00						
DATASET FILE NAME				PART NUMBER: V3L1D3J7B25BGA0		
13A095EA_DC02/00A						
				REF NUMBER:		
				EMEA00B12		
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
PJST	05/27/14	JPMC	N/A			A