




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ITEM NO.	PART NO.	DESCRIPTION	QTY.
1	SINGLE PHASE	SINGLE PHASE MONITOR DISPLAY	1
2	CABLE - 3 METERS	3 METER CABLE LENGTH	1
3	COMMANDO PLUG	32 AMP, 3 PIN, MALE	1
4	C13	10 AMP IEC	22
5	C19	16 AMP IEC	3
6	MAX 10 AMP FUSE HOLDER	FITTED WITH 10 AMP FUSE	25
7	NEON	RED NEON	25

DEFAULT OUTLETS STATE FOR CONTROLLABLE PDU	ON
INTERNAL POWER SUPPLY	YES
COMMUNICATION MODE	RS485



DETAIL A  
SCALE 1:4

TITLE				32AMP, SINGLE PHASE, VERTICAL,SINGLE PHASE, 32 AMP COMMANDO ON 3 METER FLY LEAD, 21x C13, 3x C19 IND FUSE & NEON, 1x C13 FUSE NEON ALWAYS ON, MONITOR & CONTROL	
CUSTOMER DRAWING					
ITEM REVISION NAME		13A095EB/00			
DATASET FILE NAME		13A095EB_DC02/00A			
				PART NUMBER:	
				V3L1D3J7X25BFA0	
				REF NUMBER:	
				EMEAOOB11	
DRAWN BY	DATE	CHK	SCALE	SIZE	
PJST	05/27/14	JPMC	N/A	SHT 1 OF 1	
				A	

R	05/27/14	PJST	JPMC	TSB	RELEASED TO PRODUCTION	13A095EB-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN