




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PVO-M10APU24	1.2 LBS EA.(1523g EA.)

NOTES:

1. CONTACT TECHNICAL SUPPORT FOR APPLICATIONS.
2. CONTACT TECHNICAL SUPPORT FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN BRACKETS ARE IN METRIC.
4. PART INCLUDES:
 - (1) PANVIEW 10 ANGLED PATCH PANEL NON GROUNDED
 - (6) ENGLISH 12-24 X1/2" PHILIPS HEX WASHER HEAD SCREWS.
 - (6) METRIC M6X1.0X16mm PHILIPS HEX WASHER HEAD SCREWS.
 - (1) ULTIMATE 1D LABEL KIT.
 - (1) INSTRUCTION SHEET.




PANDUIT P/N	WEIGHT
PVO-M10APU24	1.2 LBS EA.(1523g EA.)

PANVIEW 10 MODULAR INTELLIGENT
ANGLED PATCH PANEL, UNSHIELDED,
24 PORTS CUSTOMER DRAWING



PANDUIT
CORP.
TINLEY PARK, ILL. 60477



ALL DIMENSIONS ARE GIVEN IN INCHES.
UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.XX) ±.03 (XXX) ±.005
(.XX) ±.01 ANGLES ± 1°

ASSY METHOD/ TEST METHOD
N/A
SCALE
FULL

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	MAT'L	SEE NOTES ABOVE	DRAWING NO.
1	10/09/08	ALP	MJD	A:RMVD /N FROM PANDUIT PART NUMBER B:UPDATED PRODUCT TITLE	02983-04	MJD	MJD						
R	04/10/08	ALP	MJD	RELEASED TO PRODUCTION	02983-04	MJD	MJD						
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	MAT'L	SEE NOTES ABOVE	DRAWING NO.