

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

## NOTES:

- \*\*1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. CONSTRUCTED WITH CAT6A SCREENED 9 WIRE, FOUR SHIELDED TWISTED PAIR PLUS A 9<sup>TH</sup> WIRE, STRANDED 26AWG LSZH CABLE.
3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUG AND 1-9<sup>TH</sup> POSITION CONTACT AT BOTH ENDS.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

PANDUIT PART NUMBER	MINIMUM CABLE LENGTH	WEIGHT
PVSTP6X1MB**	1 METER	68g/EACH
PVSTP6X2MB**	2 METERS	115g/EACH
PVSTP6X3MB**	3 METERS	156g/EACH
PVSTP6X5MB**	5 METERS	234g/EACH
PVSTP6X10MB**	10 METERS	433g/EACH


EIA/TIA T568B WIRING SCHEME	
PLUG POSITION	CABLE WIRE
1	ORANGE/WHITE
2	ORANGE
3	GREEN/WHITE
4	BLUE
5	BLUE/WHITE
6	GREEN
7	BROWN/WHITE
8	BROWN


PART NUMBER	PRODUCT SPEC/PKG SPEC
PVSTP6X*MB**	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE

## PANVIEW TX6A 10 GIG SHIELDED (LSZH) PATCH CORD

CUSTOMER DRAWING

ITEM REVISION NAME		003 POWER DRAWING		<div>PANDUIT</div>
M02489AC/00				
DATASET FILE NAME		M02489AC_DC03/00D		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .x ± .1 [ 2.54 ]                      .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ]                      ANGLES ± 5 °  <div></div> THIRD ANGLE PROJECTION				MATERIAL:
				DRAWING NUMBER:  02489-03
DRAWN BY	DATE	CHK	SCALE	SIZE
MLJ	10-03-06	DCK	NONE	A
SHT 1 OF 1				



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	1-31-04	BJN	MAT0	EJH	UPDATED	02489-03