


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






DETAIL A
(SCALE 4X)

PANDUIT P/N	WEIGHT
QZ1B2W6BN24R	17 lb (7.7 kg)

- NOTES:
1. IDENTIFICATION: VERTICAL, MIXED (18) C-13 & (6) C-19 NETWORKED 208V / 60A / 3-PHASE DELTA POU
 2. ACCESSORY COMPONENTS:
 - (4) 10-32 x 1/2" MOUNTING SCREWS
 - (4) 10-24 x 1/2" MOUNTING SCREWS
 - (2) #10-32 LOCKING COLLAR SCREWS
 - (2) L-BRACKETS
 3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
 4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY (PVQ-RD).
 5. UL® & c-UL® LISTED 60950.
 6. RoHS COMPLIANT.
 7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 8. MAXIMUM AVAILABLE INPUT POWER = 17.3 KW
 9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

TOOLLESS MOUNTING
BUTTON 2X




PLUG
60 AMP, 250V x 3~ DELTA
3P/4W
IEC 60309, WATERTIGHT

EIGHTEEN (18)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

00A	1-19-16	MRWA	EDM	PWI	RELEASED TO PRODUCTION	09V098KR	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

TITLE VERTICAL, MIXED (18) C-13 & (6) C-19 NETWORKED POWER OUTLET UNIT CUSTOMER DRAWING						
ITEM REVISION NAME 09V098KR/00.PRT						
DATASET FILE NAME 09V098KR_DC/00A.PRT						
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:					MATERIAL:	
INCHES X.X +/- 0.03 X.XX +/- 0.018 X.XXX +/- 0.007		METRIC - MILLIMETER X. +/- 0.8 X.X +/- 0.46 X.XX +/- 0.18		ANGLE +/- 1°		
				THIRD ANGLE PROJECTION		
					DRAWING NUMBER: 09V098KR_DC	
DRAWN BY MRWA	DATE 1-19-16	CHK EDM	SCALE NONE	SHT 1 OF 1		SIZE B