


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY	MAX BUNDLE DIAMETER	LENGTH "L" ±.3 [ 7 ]
MLT2H-LP	50	2" [ 51 ]	7.9" [ 201 ]
MLT2.7H-LP	50	2.7" [ 69 ]	10.2" [ 259 ]
MLT4H-LP	50	4" [ 102 ]	14.3" [ 362 ]
MLT6H-LP	50	6" [ 152 ]	20.5" [ 521 ]
MLT8H-LP	50	8" [ 203 ]	26.8" [ 679 ]
MLT10H-LP	50	10" [ 254 ]	33.0" [ 838 ]
MLT12H-Q	25	12" [ 304 ]	39.3" [ 998 ]
MLT14H-Q	25	14" [ 355 ]	45.5" [ 1156 ]
MLT2H-TL	250	2" [ 51 ]	7.9" [ 201 ]
MLT4H-TL	250	4" [ 102 ]	14.3" [ 362 ]



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, ST3MT, HTMT
2. MINIMUM LOOP TENSILE STRENGTH - 450 LBS. (2000 NEWTONS) WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [ ] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:  
 .XXX = ±.010 [ .25 ]    .XX = ±.02 [ .5 ]  
 .X = ±.03 [ .8 ]        ANGLES = ±2°
5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED  
EDGES ALONG  
STRAP BODY


SECTION A-A  
SCALE 6:1

06A	2/12	MIM	RGRO
REV	DATE	BY	CHK

NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY

DESCRIPTION

TM



**PANDUIT**

TINLEY PARK, ILLIONS

METAL LOCKING TIE  
HEAVY SERIES -304 STAINLESS STEEL  
- CUSTOMER DRAWING -

DRAWN BY JAMB	CHK'D DPN	SCALE 2x	DRAWING NO. N41115BS_DC
------------------	--------------	-------------	----------------------------