

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT * PART NO.	NOMINAL BUNDLE DIAMETER	MAXIMUM RECOMMENDED BUNDLE DIAMETER	DIMENSIONS			WEIGHT lbs / 100 (g) / ft.
			"A" (Ref)	"B" (Ref)	"C"	
PW38_----	0.38 (9.65)	0.43 (10.92)	0.36 (9.14)	0.125 (3.18)	0.030 (0.76)	1.68 (762.0)
PW50_----	0.50 (12.70)	0.55 (13.97)	0.47 (11.94)		0.032 (0.81)	2.01 (910.00)
PW75_----	0.75 (19.05)	0.81 (20.57)	0.72 (18.29)		0.035 (0.89)	2.87 (1301.81)
PW100_----	1.00 (25.40)	1.125 (28.58)	0.81 (20.57)		0.040 (1.02)	4.47 (2027.6)
PW150_----	1.50 (38.10)	1.625 (41.28)	1.125 (28.58)		0.042 (1.07)	7.65 (3469.9)



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
NO SPLICES ALLOWED.
- DIMENSION "A" IS STATIC INSIDE DIAMETER.
DIMENSION "B" IS WIDTH OF BREAKOUT SLOTS.
DIMENSION "C" IS WALL THICKNESS.
- FLAME RETARDANT PAN-WRAP IS OFFERED IN THE FOLLOWING COLORS:

SAMPLE PART NUMBER:


PW75FR-C20

- 20 - NATURAL IN COLOR
- 20 - BLACK

0 - 25 feet (7.62 meters)
L - 50 feet (15.24 meters)
C - 100 feet (30.48 meters)
T - 200 feet (60.96 meters)
TL - 250 feet (76.20 meters)


(REFER TO CURRENT PRODUCT OFFERING
FOR OPTIONAL STANDARD PACKAGING QUANTITIES)

FR - FLAME RETARDANT POLYETHYLENE




"B"

"A" Ø



"C"



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS G03597DS_DC_GB2508BK/00B

PANDUIT

CORP. TINLEY PARK, ILLINOIS

PAN-WRAP
PW___FR-__ (Y)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

00B	8-7-09	TMSA	pk	CHANGED NOTE 3, ADDED PW38	GB2508BK	00B	pk			DRAWN BY JAD	MAT'L:	SCALE NONE
I	5-29-08	JAD		ADDED Y PARTS	GB2508BK	I				DATE 11/5/04	SEE NOTE 3	DRAWING NO. GB2508BK
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D		DWG SIZE A