






THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. THIS PART IS USED TO SNAP INTO A STANDARD U.K. LJU6C (25mm X 37.5mm) OPENING AND ACCEPTS ALL NETKEY MODULES.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT P/N	WEIGHT
NK6CS***-X	.12 LB/10 PCS (56.0 g/10 PCS)

MODEL FILENAME		M02501AA_LJ6C_ASSY_00.PRT	SIZE A	
DRAWING FILENAME		M02501AA_DC_00A.PRT		
LJU6C SHUTTERED ADAPTER CUSTOMER DRAWING				
	 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER	N/A
			PRODUCT SPEC	N/A
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.31) (.XX) ±.031(.81) ANGLES ±		WORK INSTRUCTION	N/A
			SCALE	NONE
DRAWN BY JsP	MATERIAL: ABS		PART NO.	NK6CS* *- X
DATE 1 - 30 - 06			DRAWING NO.	02501 - 01
CHK'D				

R	1-30-06	JsP		RELEASED TO PRODUCTION	02501-01				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH