



760109736 | M4800A-1U-PS

CommScope M4800A 1U Angled Panel, 48 port, for SYSTIMAX Category 5E Information Outlets and Uniprise Category 6 and 5E Information Outlets

- Available for use with the DYMO® labeling solution

Dimensions

Depth	143.00 mm		5.63 in
Height	44.45 mm		1.75 in
Width	482.60 mm		19.00 in

Electrical Specifications

ANSI/TIA Category	3		5e
-------------------	---	--	----

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Product Type	Panel, modular
Brand	CommScope®
Color	Black
Package Quantity	1
Rack Type	EIA 19 in
Rack Units	1

Mechanical Specifications

Panel Style	Angled
Material Type	High-impact, flame retardant, thermoplastic Steel

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

