

Momentum 6 Cassette, Multimode, 50/125, 0.3U, 12 fiber, LC Quad adapters, 1 MPO (M), LOMF

OR-M6LCQ12-50E



Momentum 6 modular fiber optic pre-terminated cassettes provide the same rapid deployment as our Momentum 2 and Momentum 4 products in an even higher density capability. The rugged metal housing offers additional durability and integrated bend limiting considerations to assure optimum optical performance.

features & benefits

- **Slimline cassette:** Allows for highest port density in the marketplace today.
- **Fiber port labeling:** Provides easier administration.
- **Pre-terminated solution:** For fastest installation, highest performance and consistent factory quality.

specifications

General Info

Available Internationally: Yes
Number Of Ports: 12
Typical Applications: Multimode
Connection Type: MPO-LC
Installation Destination: Fiber Cabinets
Product Series: Momentum 6

Dimensions

Depth Metric: 159
Depth U S: 6.25
Height Metric: 11
Height U S: 0.45
Length U S: 3.5

Length Metric: 89
Width Metric: 88
Width U S: 3.46
Overall Dimensions U S: 6.25x3.46x.45
Rack Units: 0.3
Height: 0.46

Cord Information

Fiber Type: 50/125 LOMF
Max Insertion Loss: 0.5
Max Return Loss: 20
Pinning: M (pinned)

Technical Information

Fiber Capacity: 12
Capacity: Ultra High Density
Equipment Type: Pre-Terminated Cassettes