



SRS-STHT-NUNU-YL-A  
SpeedPRO™ Straight Solid Channel with hinged cover, 100 mm x 100 mm (4 in x 4 in), 2 m (6 ft 6 in) length, yellow

## Dimensions

System Dimensions	100 mm x 100 mm   4 in x 4 in
Height	122.0 mm   4.8 in
Length	2000.0 mm   78.7 in
Width	120.0 mm   4.7 in
Weight	3.38 kg   7.45 lb

## Environmental Specifications

Flammability Rating	UL 94 V-0
Halogen Characteristics	LSZH
Safety Standard	UL

## General Specifications

Product Type	Solid channel with hinged cover
Color	Yellow
Brand	SpeedPRO™
Minimum Order Quantity	1
Package Quantity	1
Section Type	Straight section
Warranty	20 years

## Mechanical Specifications

Material Type	PPO/PS
---------------	--------

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

