

**CPCSSX2-06 | 360GS10E-OR****GigaSPEED X10D® 360GS10E Solid Cordage Modular Patch Cord, Orange Jacket**

Ordering Details

| Complete Part Number | Complete Description Code | Cord Length |
|----------------------|---------------------------|-------------|
| CPCSSX2-06F007 | 360GS10E-OR-7FT | 7 ft |

Dimensions

| | |
|----------------------|---------------|
| Cord Length, maximum | 100 ft 30 m |
| Cord Length, minimum | 1 m 3 ft |

Electrical Specifications

| | |
|------------------------|----------|
| ANSI/TIA Category | 6A |
| dc Resistance, maximum | 0.30 ohm |
| Safety Voltage Rating | 300 V |

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Environmental Space | Non-plenum |
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Safety Standard | cETL ETL |

General Specifications

| | |
|--------------------------------|---|
| Cable Type | U/UTP (unshielded) |
| Interface, connector A | RJ45 plug |
| Interface, connector B | RJ45 plug |
| Jacket Color | Orange |
| Brand | GigaSPEED X10D® SYSTIMAX 360™ SYSTIMAX® |
| Interface Feature, connector A | Standard |
| Interface Feature, connector B | Standard |
| Package Quantity | 1 |
| Pairs, quantity | 4 |

Mechanical Specifications

| | |
|-------------------------------|------------------------------|
| Conductor Type | Solid |
| Material Type | Copper alloy Polycarbonate |
| Outlet/Module Contact Plating | Precious metals |
| Plug Insertion Life, minimum | 750 times |
| Plug Retention Force, minimum | 133 N 30 lbf |
| Wiring | T568B |

Wiring Diagram

| | Connector A | Connector B |
|------------|--------------|--------------|
| Position 1 | White/Orange | White/Orange |
| Position 2 | Orange | Orange |
| Position 3 | Lt. Green | Lt. Green |
| Position 4 | Blue | Blue |
| Position 5 | Lt. Blue | Lt. Blue |
| Position 6 | Green | Green |
| Position 7 | Lt. Brown | Lt. Brown |
| Position 8 | Brown | Brown |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2008

Classification

Compliant

Designed, manufactured and/or distributed under this quality management system



Included Products

860474303 | 1095B OR 4/24 RVAR (Product Component—not orderable) — GigaSPEED X10D® 1095B Category 6A U/UTP Cable, non-plenum, orange jacket, 4 pair count, variable length, reel