



CC0057570/1 | UNP610-WM-12P Uniprise® Category 6 Patch Panel, Wall Mount, 12 port

- Available for use with the DYMO® labeling solution

Replaced By

760183079
UNPWM-U-610-12P-M Uniprise Wall Mount Universal Cat6 Panel 12 Port Metal Bracket

Dimensions

Depth	50.80 mm 2.00 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	254.00 mm 10.00 in
Width	81.28 mm 3.20 in

Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	cUL UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Intelligence Type	Passive
Total Ports, quantity	12
Cable Type	U/UTP (unshielded)
Product Type	Panel
Brand	Uniprise®
Color	Black

CC0057570/1 | UNP610-WM-12P

Modules, quantity	2
Package Quantity	1
Rack Type	EIA 19 in

Mechanical Specifications

Conductor Gauge, solid	22 AWG 23 AWG 24 AWG 26 AWG
Conductor Gauge, stranded	22 AWG 23 AWG 24 AWG
Conductor Type	Solid Stranded (7 strands)
Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
Outlet/Module Contact Plating	Precious metals
Plug Insertion Life, minimum	750 times
Plug Insertion Life, test plug	IEC 60603-7 compliant plug
Plug Retention Force, minimum	30 lbf 133 N
Rear Termination Contact Plating	Nickel
Rear Termination Type	IDC
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

