

111-02304

HellermannTyton

Article Number: 111-02304



Description: Standard Cable Tie, 5.5" Long, 18lb Tensile Strength, PA66VO, Natural, 1000/pkg

Base Data		
	Local Order Number	T18I9VOM4
	Type	T18I
	Color	Natural (NA)
	Features and Benefits	• Flame retardant cable ties are self extinguishing and provide low smoke emissions. • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
	Quantity Per	bag
	Product Description	HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Standard Cable Tie, 5.5" Long, 18lb Tensile Strength, PA66VO, Natural, 1000/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	18.0lbs
	Minimum Tensile Strength (Metric)	80.0N
	Length L (Imperial)	5.5"
	Length L (Metric)	140.0mm
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.1"
	Width W (Metric)	2.5mm
	Bundle Diameter Min. (Imperial)	0.118"
	Bundle Diameter Min. (Metric)	3.0mm

111-02304



Product Dimensions	Bundle Diameter Max. (Imperial)	1.38"
	Bundle Diameter Max. (Metric)	35.0mm
Material and Specifications		
	Material	Polyamide 6.6 V0 (PA66V0)
	Material Shortcut	PA66V0
	Flammability	UL94 V0
	Halogenfree	Yes
	Operating Temperature	-40°F to +185°F (-40°C to +85°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Metric)	1000
	Customs Number(Schedule B)	3926909987