



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. PART NUMBERS: SEE SHEET 2 FOR ALL PART NUMBERS.
4. CASSETTE WEIGHT: 6.2oz (175g)



FIBER POSITION FROM LC END TO MPO END																								
METHOD A 24F MPO CASSETTE (AS)																								
LC PORT NUMBER	1		2		3		4		5		6		7		8		9		10		11		12	
	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A
MPO #1	1	13	2	14	3	15	4	16	5	17	6	18	7	19	8	20	9	21	10	22	11	23	12	24
METHOD A FLIPPED 24F MPO CASSETTE (AF)																								
LC PORT NUMBER	1		2		3		4		5		6		7		8		9		10		11		12	
	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A
MPO #1	13	1	14	2	15	3	16	4	17	5	18	6	19	7	20	8	21	9	22	10	23	11	24	12
METHOB B 24F MPO CASSETTE (BN)																								
LC PORT NUMBER	1		2		3		4		5		6		7		8		9		10		11		12	
	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A	B	A
MPO #1	24	12	23	11	22	10	21	9	20	8	19	7	18	6	17	5	16	4	15	3	14	2	13	1

TITLE

HD FLEX CASSETTE, 12-PORT
DUPLX LC TO (1) 24-FIBER MPO

CUSTOMER DRAWING

ITEM REVISION NAME

12F187MD/03

DATASET FILE NAME

12F187MD_DC/03A


UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN (mm)

.x ± .1 [2.54]

.xxx ± .005 [.127]

.xx ± .01 [.25]

ANGLES ± 5 °



THIRD ANGLE
PROJECTION

MATERIAL:

DRAWING NUMBER:

12F187MD-DC

00	09-16-16	SAT	TMSE	EJH	RELEASED TO PRODUCTION	12F187MD-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	SIZE
SAT	09-08-16	TMSE	NONE		A

