




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:


1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN BRACKETS ARE METRIC.
3. ENCLOSURE MATERIAL: GALVANNEALED STEEL
ENCLOSURE COLOR: BLACK
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. SEE SHEET 2 FOR CASSETTE PORT OPTIONS.
6. PART WEIGHT 2.3 lbs (1 kg)



EQUIPMENT RAIL ADAPTER REMOVED




WITH EQUIPMENT RAIL ADAPTER



WITH EQUIPMENT RAIL ADAPTER


01	10-04-16	SAT	BONS	TMK	RELEASED TO PRODUCTION		15F318AJ-DC
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN

TITLE HD FLEX ORU BRACKET AND CASSETTE HOLDER CUSTOMER DRAWING							
ITEM REVISION NAME 15F318AJ/02						PANDUIT	
DATASET FILE NAME 15F318AJ_DC/02A							
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) DIMENSIONS ARE FOR REFERENCE ONLY						PART NO: FLEX-ORUBR**	
 THIRD ANGLE PROJECTION						DRAWING NUMBER: 15F318AJ-DC	
						DRAWN BY BONS	DATE 8-5-16


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FLEX-ORUBR04



FLEX-ORUBR06



FLEX-ORUBR12

B

B



A


A

01	10-04-16	SAT	BONS	TMK	RELEASED TO PRODUCTION			15F318AJ-DC	
REV	DATE	BY	CHK	APR	DESCRIPTION			ECN	

TITLE HD FLEX ORU BRACKET AND CASSETTE HOLDER CUSTOMER DRAWING									
ITEM REVISION NAME 15F318AJ/02					PART NO: FLEX-ORUBR**				
DATASET FILE NAME 15F318AJ_DC/02A					DRAWING NUMBER: 15F318AJ-DC				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) DIMENSIONS ARE FOR REFERENCE ONLY									
DRAWN BY BONS			DATE 8-5-16		CHK SAT		SCALE 1:4		SHT 2 OF 2
									A

2

1



THIRD ANGLE PROJECTION