

LM-215

21.5" LED Monitor

21.5" LED Screen Size, 1920 x 1080 Resolution, OSD, Audio Input, Internal Speakers, VESA Compatible.



LM-215

Key Features

- Versatile Connectivity – DVI, VGA, HDMI, Audio In
- Built-In Image Enhancer: 3D Comb Filter / Deinterlace / Noise Reduction
- Fast Response Time (5ms)
- Selectable between 4:3 & 16:9 Aspect Ratio
- Audio Input, Internal Speakers, VESA Compatible
- On-Screen Display Menu
- Desk Stand (Detachable)
- Selectable Signal Source
- VESA Standard Wall Mount
- HDMI Cable Provided

Technical Specification

Model Number	LM-215
Resolution	1920 (H) x 1080 (V)
Active Display Area	476.64 (W) x 268.11 (H) mm
Pixel Pitch	0.2482 x 0.2482 mm
Contrast Ratio	1000:1
Brightness	200 cd/m ²
Response Time	5ms
Viewing Angle	Up/Down: 160°, Left/Right: 170°
Backlight Life	40,000 Hours
Compatibility	PC Compatible
Display Colours	16.7 Million
Speaker	Multimedia Speaker
Number of Speaker	8Ω, 2W x2
Connector	HDMI x 1, VGA x1, DVI x1
Audio Interface	Audio In x1
Power Interface	AC In x1
OSD	Yes
Certification	CE / ROHS / UL
Power Supply	Built-In
Power Consumption	<30W in ON Mode
Voltage	100V - 240V, AC60/50Hz
Work Humidity	20% - 70%
Work Temperature	-10°C to 50°C
VESA	Yes (100 x 100 mm)
Dimensions (W x H x D)	513 x 310 x 50 mm
Weight	3.8 kg

Genie CCTV reserves the right to change specifications without notice. Please contact your representative to confirm current specifications.