

LM-32

32" LED Monitor

*32" LED Screen Size, 1920 x 1080 Resolution,
OSD, Audio Input and VESA Compatible.*



LM-32

Key Features

- Versatile Connectivity – DVI, VGA, HDMI, Audio In
- Built-In Image Enhancer: 3D Comb Filter / Deinterlace / Noise Reduction
- Selectable between 4:3 & 16:9 Aspect Ratio
- On-Screen Display Menu
- Desk Stand (Detachable)
- Selectable Signal Source
- VESA Standard Wall Mount
- HDMI Cable Provided

Technical Specification

Model Number	LM-32
Resolution	1920 x 1080
Active Display Area	698(H) x 393(V) mm
Pixel Pitch	121(H) x 364(V) mm
Contrast Ratio	1000:1
Brightness	200cd/ m2
Response Time	8 ms
Viewing Angle	178°/178°
Backlight Life	30,000 Hours
Compatibility	PC Compatible
Speaker	Not available
Connector	(x1) VGA IN, (x1) DVI IN and (x1) HDMI IN
Audio Interface	Audio In x1
Power Interface	AC In
OSD	Yes
Certification	CE / FCC
Power Consumption	<40W(on), 0.5W(off)
Voltage	100-240V and 60/50Hz
Work Humidity	10% - 80%
Work Temperature	0°C - 40°C
VESA	75 x 75 mm
Dimensions (W x H x D)	721 x 171 x 507 mm
Weight	8.5Kgs

Genie CCTV reserves the right to change specifications without notice. Please contact your representative to confirm current specifications.

Dimensions (mm)

