



553947-1

Undercarpet Direct Connecting Receptacle, 3-conductor, duplex, black

Body Features

Color Black

Configuration Features

Ground Configuration Standard

Number of Conductors 3

Number of Ports 1

Port Style Duplex

Dimensions

Height 25.654 mm | 1.010 in

Width 159.258 mm | 6.270 in

Electrical Characteristics

Current Rating 20 A

Voltage Rating 300 Vac

Industry Standards

Standards Compliance UL 498

UL File Number E73213

Mechanical Attachment

Mounting Style Floor | Surface

Packaging Features

Packaging Quantity 1

Product Availability

Region Latin America | North America

Product Type Features

Product Type Floor Fitting Kit

Product Category Power Outlets

Kit Type Direct Connecting Receptacle

Product Classification Fittings - Floor

Signal Configuration Power

553947-1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant