



554192-1

**Undercarpet Dual Duplex Receptacle DCR Kit, 3 conductors, 2 ports, black**

## Body Features

Color Black

## Configuration Features

Ground Configuration Standard

Number of Conductors 3

Number of Ports 2

Port Style Duplex

## Dimensions

Height 25.654 mm | 1.010 in

Width 159.258 mm | 6.270 in

## Electrical Characteristics

Current Rating 20 A

Voltage Rating 300 Vac

## Industry Standards

Standards Compliance UL 498

UL File Number E73213

## Mechanical Attachment

Mounting Style Floor | Surface

## Packaging Features

Packaging Quantity 1

## Product Availability

Region Latin America | North America

## Product Type Features

Product Type Floor Fitting Kit

Product Category Power Outlets

Kit Type Direct Connecting Receptacle

Product Classification Fittings - Floor

Signal Configuration Power

554192-1

## Regulatory Compliance/Certifications

---

**Agency**

RoHS 2011/65/EU

**Classification**

Compliant