



CompuLink fiber optic patch cord

LC (ceramic) to LC (ceramic) 2-fiber orange jacketed 62.5/125 OM1 riser rated zipcord.

- * Premium performance, exceeds EIA/TIA-568 specifications with maximum insertion loss of less than 0.5 dB.
- * Built using Corning connectors and cordage.
- * Individually bagged.

ANIXTER PART No.	VENDOR PART No.	LENGTH FT.	LENGTH MT.
246811	LCCLCCD1	3.3 FT.	1 MT.
246812	LCCLCCD2	6.6 FT.	2 MT.
246813	LCCLCCD3	10.0 FT.	3 MT.
275067	LCCLCCD4	13.1 FT.	4 MT.
246814	LCCLCCD5	16.4 FT.	5 MT.
275070	LCCLCCD6	19.7 FT.	6 MT.
266847	LCCLCCD7	23.0 FT.	7 MT.
275071	LCCLCCD8	26.2 FT.	8 MT.
246815	LCCLCCD10	32.8 FT.	10 MT.
275072	LCCLCCD12	39.4 FT.	12 MT.
275073	LCCLCCD15	49.2 FT.	15 MT.
275074	LCCLCCD18	59.1 FT.	18 MT.
305923	LCCLCCD20	65.6 FT.	20 MT.

NOTICE: THIS COMPULINK DRAWING IS BEING PROVIDED FOR PURPOSES OF PROPOSAL AND DESIGN DISCUSSION ONLY. COMPULINK RECOGNIZES THAT THE CUSTOMER MAINTAINS DESIGN AUTHORITY OVER THE SUBJECT PRODUCT AND AS SUCH, THE CUSTOMER MAINTAINS FULL RESPONSIBILITY FOR DESIGN EVALUATION, APPROVAL, AND QUALIFICATION. COMPULINK DRAWINGS ARE PROVIDED FOR REFERENCE ONLY AND ARE NOT TO BE USED FOR SPECIFICATION OR DESIGN CONTROL PURPOSES.

CONFIDENTIAL: THE CONTENTS OF THIS DRAWING ARE CONFIDENTIAL AND CONSTITUTE THE EXCLUSIVE PROPERTY OF COMPULINK CABLE ASSEMBLIES INC. THIS DRAWING'S CONTENTS MAY NOT BE MADE PUBLIC IN ANY MANNER, DISTRIBUTED OR LOANED TO OTHERS OR REPRODUCED OR COPIED EITHER IN WHOLE OR PART WITHOUT THE PRIOR WRITTEN CONSENT OF THE COMPANY.

REV	DESCRIPTION	DATE	BY

DRAWN: G.KRUG	DATE 1/13/12
CHECKED: DATE	
APPROVALS	DATE
ENGINEERING: DATE	
QUALITY: DATE	



CADD REF. No.:
LCLCOM1RISER

DRAWING NO.
LC-LC-OM1-RISER