# **Product Specifications**





MP-5EU-1 | 6-569278-3

Modular Plug Kit, category 5E, 8P/8C, unshielded, 4.8 – 5.6 mm max cable jack OD, 8-position, 100/bag

### **Body Features**

Conductor Type Solid | Stranded

#### **Configuration Features**

Number of Positions 8
Keyed No

#### **Contact Features**

Contact Base Material Phosphor bronze

Contact Mating Area Plating Material Gold

Contact Mating Area Plating Thickness 50.00 µin | 1.27 µm

Number of Contacts Loaded 8

#### **Dimensions**

Cable Jacket Outside Diameter Range 0.190–0.220 in | 4.8–5.6 mm

Conductor Outside Diameter 0.034–0.039 in | 0.86–0.99 mm

Conductor Wire Size 26–23 AWG

#### **Housing Features**

Housing Material Glass filled polycarbonate

#### **Industry Standards**

UL Flammability Rating UL 1863

# **Packaging Features**

Packaging Quantity 100

## **Product Availability**

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

#### **Product Type Features**

Cable Type Round, unshielded

Performance Category Category 5e

Connector Style Plug
Jack Type RJ45
Latch Style Standard

# Product Specifications



MP-5EU-1 | 6-569278-3

Product Type Connector
Shielded No

#### **Termination Features**

Termination Method to Wire/Cable Insulation Displacement Crimp (IDC)