

EZ PATCH

Ortronics® patent pending EZ Patch solution is a revolutionary way to dispense and manage patch cords, reducing installation time and waste. There are no bags to open, tie wraps to undo or straightening necessary; the cords dispense one after another, ready to install.

CLARITY 6A			
Part Number	Description	Contains Part Number	Qty Per Carton
EZC6A03Q50-XX	EZ Patch Clarity 10G modular patch cord, 3'	OR-MC610003-XX	50
EZC6A05Q50-XX	EZ Patch Clarity 10G modular patch cord, 5'	OR-MC610005-XX	50
EZC6A07Q40-XX	EZ Patch Clarity 10G modular patch cord, 7'	OR-MC610007-XX	40
EZC6A09Q30-XX	EZ Patch Clarity 10G modular patch cord, 9'	OR-MC610009-XX	30
EZC6A15Q20-XX	EZ Patch Clarity 10G modular patch cord, 15'	OR-MC610015-XX	20

To order standard colors, replace xx suffix: -06 = blue; -05 = green; and EZC6A15Q20-XX is only available in -06 = blue

CLARITY 6			
Part Number	Description	Contains Part Number	Qty Per Carton
EZC603Q50-XX	EZ Patch Clarity 6 modular patch cord, 3'	OR-MC603-XX	50
EZC605Q50-XX	EZ Patch Clarity 6 modular patch cord, 5'	OR-MC605-XX	50
EZC607Q50-XX	EZ Patch Clarity 6 modular patch cord, 7'	OR-MC607-XX	50
EZC609Q40-XX	EZ Patch Clarity 6 modular patch cord, 9'	OR-MC609-XX	40
EZC610Q40-XX	EZ Patch Clarity 6 modular patch cord, 10'	OR-MC610-XX	40
EZC615Q25-XX	EZ Patch Clarity 6 modular patch cord, 15'	OR-MC615-XX	25

To order standard colors, replace xx suffix: -09 = white; -08 = gray; -06 = blue; -05 = green; -04 = yellow; -02 = red
EZC610Q40-XX is available in -06 = blue; -05 = green and -04 = yellow only
EZC615Q25-XX is available in -06 = blue; -05 = green; -04 = yellow and -02 = red only

CLARITY 5E			
Part Number	Description	Contains Part Number	Qty Per Carton
EZC5E03Q50-XX	EZ Patch Clarity 5E modular patch cord, 3'	OR-MC5E03-XX	50
EZC5E05Q50-XX	EZ Patch Clarity 5E modular patch cord, 5'	OR-MC5E05-XX	50
EZC5E07Q50-XX	EZ Patch Clarity 5E modular patch cord, 7'	OR-MC5E07-XX	50
EZC5E09Q40-XX	EZ Patch Clarity 5E modular patch cord, 9'	OR-MC5E09-XX	40
EZC5E10Q40-XX	EZ Patch Clarity 5E modular patch cord, 10'	OR-MC5E10-XX	40
EZC5E15Q25-XX	EZ Patch Clarity 5E modular patch cord, 15'	OR-MC5E15-XX	25

To order standard colors, replace xx suffix: -09 = white; -08 = gray; -06 = blue; -05 = green; -04 = yellow
EZC610Q40-XX and EZC5E15Q25-XX are available in -06 = blue; -05 = green and -04 = yellow only



EZ Patch

INDIVIDUAL JACKS

TracJack® modules combine the ease and reliability of a front-loading individual jack with preferred 110 termination and offer universal T568A/B wiring. High density jacks offer a friendly lacing cap terminating method for termination tools and rugged rear loading design.

TRACJACK® HIGH DENSITY JACKS	
Part Number	Description
OR-TJ6A	Clarity 6a jack, 8-position, 180° exit, fog white
OR-TJ600	Clarity 6 jack, 8-position, 180° exit, fog white
OR-TJ5E00	Clarity 5e jack, 8-position, 180° exit, fog white

FACEPLATES	
Part Number	Description
OR-40300545	Holds six TracJacks, 2.75" x 4.5", plastic
OR-403STJ14	Holds four TracJacks, 2.75" x 4.5", stainless steel
OR-403STJ16	Holds six TracJacks, 2.75" x 4.5", stainless steel
OR-404TJ6	Holds six TracJacks, 6.98" x 4.33" x 1.16" Note: Includes internal storage ring for fiber and two TracJack blanks. Can mount directly to single or double gang recessed wall boxes.

CLARITY HIGH DENSITY JACKS & FACEPLATES	
Part Number	Description
OR-403HDJ13	Faceplate single gang, 3 port, fog white, rear load, with designation

NOTE: Call for other colors.



OR-TJ600



OR-404TJ6



OR-403STJ14