



SAVI 700 SERIES

Multiple devices. Singular control.

The Savi 700 series is changing the way productivity-focused office professionals communicate. With multi-device connectivity, an ultra-versatile convertible headset, and up to 350 feet of wireless range, now you can easily manage PC, mobile and desk phone calls with the most intelligent wireless headset system on the market.

Multi-device connectivity

SAVI 700 SERIES



- A One-touch vol +/-, mute, flash
- B One-touch call answer/end
- C Hot swappable battery¹ for unlimited talk time
- D Noise-canceling microphone



SAVI 740
Convertible



SAVI 730
Over-the-ear



SAVI 720
Over-the-head
(binaural)



SAVI 710
Over-the-head
(monaural)

SUPERIOR CALL MANAGEMENT

- 3-way connectivity to easily switch and mix PC, mobile, and desk phone audio
- Automatically routes mobile audio to whichever device you pick up
- Easily transfer audio between headset and mobile phone to take calls on-the-road
- UC presence automatically updated when on a PC, mobile, or desk phone call
- Energy efficient adaptive power system optimizes for range and talk time
- Conference in up to three additional headsets and guests can continue through multiple calls

SAVI 740 INNOVATIVE DESIGN

- Lightest DECT wireless headset on the market
- Three comfortable wearing styles
- Hot swappable battery¹ for unlimited talk time

ADVANCED DECT WIRELESS SECURITY

- Keep calls and information safe and secure with the latest DECT security certification
- Most secure DECT headset on the market certified by DECT forum

PREMIUM SOUND QUALITY

- Advanced wideband audio using CAT-iq technology for high definition voice quality
- Noise-canceling microphone reduces background noise interruptions

- Enhanced Digital Signal Processing (DSP) provides more natural voice sounds

RECOMMENDED ACCESSORIES

- Use with Electronic Hookswitch Cable or Handset Lifter to remotely answer/end calls

GLOBAL CUSTOMER CARE

Backed by Plantronics industry leading global service and support.

(800) 544-4660 (US and Canada)

(831) 458-7700 (outside US)

For more information about the Savi 700 Series, please visit our website at plantronics.com.



OPTIMIZED FOR UNIFIED COMMUNICATION

Connects to	PC + mobile + desk phone
Ideal for	Professionals who use a mix of PC, mobile and desk phone communications while in the office for conference calls, webinars, video conferencing, and listening to multimedia
Talk time	Up to 7 hr (W740) ¹ ; Unlimited (W745) ¹ ; Up to 6 hr (W730); Up to 13 hr (W710, W720)
Headset weight	W740/745 Convertible: 21 g; W730 Over-the-ear: 25 g; W710 Over-the-head (monaural): 74 g; W720 Over-the-head (binaural): 96 g
Security	64-bit encryption, DECT Security Certified
Wireless frequency	DECT 6.0, range up to 350 ft between headset and base; Bluetooth® v2.1 connection between mobile phone and base
Audio performance	PC + desk phone Wideband: up to 6,800 Hz
Hearing protection	SoundGuard DIGITAL: protects against sound levels above 118 dBA; Anti-startle (detects and eliminates any large sudden increase in signal level); Time-Weighted Average prevents average daily noise exposure level from exceeding 85 dBA SoundGuard: (W730) protects against sound levels above 118 dBA
Limited warranty	1 yr
Models	W740 (convertible); W745 (convertible + deluxe charging cradle kit); W730 (over-the-ear); W720 (over-the-head, binaural); W710 (over-the-head, monaural); UC Standard version for softphones from Avaya, Cisco, IBM, Skype and more ² W740-M; W745-M; W730-M; W720-M; W710-M Version optimized for Microsoft Lync

¹ Unlimited talk time with deluxe charging cradle kit, comes standard with Savi 745. Available as an accessory with Savi 740.

² Download the latest release of Plantronics Hub to get one-touch call answer/end with these softphones.