

760042960 | MIR-RJ45
M-Series Ruggedized Receptacle, RJ45

General Specifications

Product Type	Adapter
Application	Provides sealed copper connectivity
Color	Black
Package Quantity	1
Total Ports, quantity	1

Dimensions

Depth	25.40 mm 1.00 in
Height	35.56 mm 1.40 in
Weight	0.02 kg 0.05 lb
Width	35.56 mm 1.40 in

Mechanical Specifications

Material Type	High-impact, flame retardant, UL-rated 94 V-0, thermoplastic
---------------	--

Electrical Specifications

ANSI/TIA Category	5e 6 6A
-------------------	-------------

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-25 °C to +85 °C (-13 °F to +185 °F)
Safety Standard	cUL UL

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system