

**E/EW/EWZ**  
**E103B: 24 HOUR CONTROL**  
**EW103B: 7 DAY CONTROL**  
**EWZ103: 7 DAY ASTRO**

## APPLICATIONS



Versatile Control: lighting, signs, pumps, motors, fans, heating, and air-conditioning, security systems.



**DETECTS INPUT VOLTAGE AUTOMATICALLY!**  
**ACCURATE TO THE MINUTE!**

## FEATURES

- **AUTOMATIC** input voltage detection
- 20 events for programs
- Automatic Daylight Savings adjustment
- Power Outage Backup: **SUPERCAPACITOR** no batteries to replace
- **2-in-1** DPST Contacts – also use as SPST
- **LED INDICATORS** – Red for load status
- 40 AMP contact
- Manual Override ON & OFF

## SPECIFICATIONS

**MULTI-VOLTAGE INPUT:**  
 120/208-240/277VAC  
 (automatic detection)

**OPERATING TEMPERATURE:**  
 -40°F to +149°F (-40°C to +65°C)

**ENCLOSURE:**  
 Indoor/Outdoor NEMA 3R polycarbonate



## RATINGS

- 40A General Purpose @ 120-277VAC
- 40A Inductive @ 120-277VAC
- 30A Ballast @ 120VAC
- 20A Ballast @ 208-277VAC
- 15A Tungsten @ 120VAC
- 1HP @ 120VAC
- 1 1/2 HP @ 208VAC
- 2HP @ 240 - 277VAC
- 720VA Pilot Duty @ 120-277VAC
- 30A Resistive @ 28VDC

