LIGHTING Medium Wallpacks WPM SERIES



FEATURES

- --- For warehouse, perimeter lighting, security, and retail.
- Die cast housing and lens frame with powdercoat finish and a porcelain medium base socket assembly.
- ---- Front frame is hinged with one piece stippled aluminum reflector.
- Heat and shock resistant borosilicate glass lens, silicone gasketing.
- Listed for wet location use.
 - Excellent for security and perimeter lighting and commercial and industrial applications.
- **—** Lamp included.

RATINGS



All dimensional data is listed in inches.

CAT. NO.	DESCRIPTION	VOLTAGE	BALLAST	HEIGHT	WIDTH	DEPTH	LAMP	BASE
WPM100MHQ	100 Watt Metal Halide	120/208/240/277VAC	QUAD HX-HPF	9	14.25	7.1	ED17	Medium
WPM150SQ	150 Watt Sodium	120/208/240/277VAC	QUAD HX-HPF	9	14.25	7.1	ED17	Medium
WPM150S	150 Watt Sodium	120VAC	R-NPF	9	14.25	7.1	ED17	Medium
WPM150MHQP*	150 Watt Metal Halide Pulse Start	120/208/240/277VAC	QUAD PULSE	9	14.25	7.1	ED17	Medium