



TracJack Plastic Surface Mount Box for two modules, Cloud White OR-404TJ2-88

OVERVIEW

Ortronics TracJack Surface Mount Outlet Boxes accept front-loading TracJack modules and provide snap-on covers and snap-in label fields. Boxes are supplied with screws and double-sided adhesive tape for mounting onto almost any surface. Compatible with Wiremold 2700, 2800 and 2900 raceway series.

FEATURES

- Low profile compact design
- Base plate and snap-on cover design
- Front-load module approach
- Textured finish
- Holds two TracJack modules
- Recessed label fields
- Compatible with LabelMO XL
- Designed to seamlessly intergrade with Wiremold 2700, 2800 and 2900 raceways

BENEFITS

- Blends with most environments
- Quick and easy to install
- Improves access for future work
- Hides future scuffs
- Supports up to two station terminations
- Supports TIA/EIA 606 labeling standard
- Computer generated labeling
- Low profile datacom raceway application

App Install Info

Mounting Hardware Included: #6-20*19 mm
(Pan head) 2ea

Dimension Info

Depth Metric: 30.48 mm
Height Metric: 57.66 mm
Width Metric: 65.79 mm
Height U S: 2.27"

General Info

Product Series: Clarity
Type: Plates and Boxes
Footprint: TracJack
Color: Cloud White
Number Of Ports: 2

Technical Info

Capacity: Up to two TracJack modules

Listing Agency Info

UL E131600

BUY AMERICAN ACT COMPLIANCE

Country of Origin: TAIWAN
Buy American Act Status: Trade Agreement
Act Compliant