



Mighty Mo Wall Mount Cabinet OR-MMW192426P-B

OVERVIEW

19U x 24"W x 26D, Plexiglass door, height is 35.75", Basic Black

FEATURES

- Cable management to support and organize cables, ensuring proper cable management for minimum distortion and maximum network performance.
- Choice of solid or plexiglass door
- The cabinet can be mounted to open left or right
- Locking center section swings out to provide easy access to the equipment
- Front and center sections are keyed alike
- Includes one pair of fully adjustable 12-24 EIA mounting rails
- Brush cable entry plates standard on top rear
- Cable knockout plates standard on bottom rear
- 3" hole with cap standard on top and bottom rear
- Vented sides for passive cooling of active equipment
- Optional 50cfm cooling fans are available to further protect active equipment
- Heavy duty 14 GA (.075") steel construction

Dimension Info

Depth U S: 26"
Height: 35.75"
Rack Units: 19
Width U S: 24"
Capacity Weight U S: 200 lbs

General Info

Product Series: Mighty Mo
Type: Cabinets
Component Type: Wall Mount Cabinets

Construction Info

Component1: Cabinet - Material1: 14 GA
(.075") steel, Finish_Plating1: Black

BUY AMERICAN ACT COMPLIANCE

Buy American Act Status: Buy American Act
Compliant