

MIGHTY MO® CABINETS

Mighty Mo Wall Mount Cabinets

NOTE: Product dimensions are listed by width, height and depth unless specified otherwise.



Mighty Mo® Wall Mount Cabinets

OR-MMW122420P-B



Mighty Mo wall mount cabinets



PART NO.	DESCRIPTION	WEIGHT CAPACITY
OR-MMW122420S-B	12U x 24" W x 20" D, Solid door, height is 23.50", Basic Black	150 lbs
OR-MMW122420P-B	12U x 24" W x 20" D, Plexiglass door, height is 23.50", Basic Black	150 lbs
OR-MMW192420S-B	19U x 24" W x 20" D, Solid door, height is 35.75", Basic Black	200 lbs
OR-MMW192420P-B	19U x 24" W x 20" D, Plexiglass door, height is 35.75", Basic Black	200 lbs
OR-MMW262420S-B	26U x 24" W x 20" D, Solid door, height is 48.00", Basic Black	300 lbs
OR-MMW262420P-B	26U x 24" W x 20" D, Plexiglass door, height is 48.00", Basic Black	300 lbs
OR-MMW122426S-B	12U x 24" W x 26" D, Solid door, height is 23.50", Basic Black	150 lbs
OR-MMW122426P-B	12U x 24" W x 26" D, Plexiglass door, height is 23.50", Basic Black	150 lbs
OR-MMW192426S-B	19U x 24" W x 26" D, Solid door, height is 35.75", Basic Black	200 lbs
OR-MMW192426P-B	19U x 24" W x 26" D, Plexiglass door, height is 35.75", Basic Black	200 lbs
OR-MMW262426S-B	26U x 24" W x 26" D, Solid door, height is 48.00", Basic Black	300 lbs
OR-MMW262426P-B	26U x 24" W x 26" D, Plexiglass door, height is 48.00", Basic Black	300 lbs

Mighty Mo wall mount cabinet accessories

PART NO.	DESCRIPTION
OR-MMCFAN-4-50	Fan Kit, 4", 50cfm
OR-MMWHMBM12-B	Rear Horizontal Mount Bracket Kit
OR-MMWBPK	Brush Plate Kit
OR-MMW12M12-B	12U Mounting Rail, 12-24, 1-pair
OR-MMW19M12-B	19U Mounting Rail, 12-24, 1-pair
OR-MMW26M12-B	26U Mounting Rail, 12-24, 1-pair