

CAT6A SHIELDED 24 PORT PANEL ANGLED, WITH INDIVIDUAL SHIELDED KEYSTONE JACKS

OR-PHATKS6A24 | [Ortronics](#)



FEATURES & BENEFITS

24 port Cat6A shielded recessed angled panel with 24 rear loading TKS6A shielded jacks. Includes rear cable management, and grounding lug. Occupies 1 rack unit of space 1.75" x 19"



- **Meets Category 6A component standard:** Ensures standards compliance.
- **Easy lace wiring** Reduces wiring time.
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion.
- **Rear loading:** preferred mounting for panels
- **Supplied rear cable management:** supports good cabling practices.
- **RoHS compliant:** Lead free.

SPECIFICATIONS

GENERAL INFO

Category Performance Application: Category 6A shielded
Color: Black & silver
Footprint: Keystone
Mod Jack Wiring: Universal T568A/B
Number Of Ports: 24
Termination: Insulation displacement contacts
Type: Patch Panels

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E131600
FCC Standard: Yes
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Angled Patch Panel

Component 2: Cast metal Cat6A jack
Component 3: Rear cable management bar
Material 1: .065 steel
Material 2: Zinc alloy housing
Material 3: round edge flat steel

DIMENSIONS

Depth (Metric): 175.7 mm
Depth (US): 6.92 in
Height (US): 1.72 in
Width (Metric): 482.6 mm
Width (US): 19.00"

TECHNICAL INFORMATION

Category Rating: Cat 6a component compliant
Performance Rating: Cat6a