
CAT6A SHIELDED 48 PORT PANEL ANGLED, WITH INDIVIDUAL SHIELDED KEYSTONE JACKS

OR-PHATKS6A48 | [Ortronics](#)



FEATURES & BENEFITS

48 port Cat6A shielded recessed angled panel with 48 rear loading TKS6A shielded jacks. Includes rear cable management, and grounding lug. Occupies 2 rack unit of space 3.5" x 19"



- **Meets Category 6A component standard:** Ensures standards compliance
- **Easy lace wiring** Reduces wiring time
- **Easy to follow universal wiring label:** Quick and user-friendly, eliminates confusion
- **Rear loading:** preferred mounting for panels
- **Supplied rear cable management :** supports good cabling practices.
- **RoHS compliant:** Lead free

SPECIFICATIONS

GENERAL INFO

Category Performance Application: Category 6A shielded
Color: Black & silver
Footprint: Keystone
Mod Jack Wiring: Universal T568A/B
Number Of Ports: 48
Termination: Insulation displacement contacts
Type: Patch Panels

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CUL Listing No: E131600
FCC Standard: Yes
UL Listing No: E131600

CONSTRUCTION INFORMATION

Component 1: Angled Patch Panel

Component 2: Cast metal Cat6A jack

Component 3: Rear cable management bar

Material 1: .065 steel

Material 2: Zinc alloy housing

Material 3: round edge flat steel

DIMENSIONS

Depth (Metric): 180.6 mm

Depth (US): 7.11 in

Height (US): 3.47 in

Width (Metric): 482.6 mm

Width (US): 19.00"

TECHNICAL INFORMATION

Category Rating: Cat 6a component compliant

Performance Rating: Cat6a