

SM8TAT2SA

Smart Managed PoE+ Switch

(8) 10/100/1000Base-T Ports + (2) 100/1000 SFP Slots



This switch is a next generation smart managed switch with 20Gbps switching capacity. It provides (8) 10/100/1000Base-T copper ports with IEEE 802.3at PoE+ capability and (2) additional 100/1000 dual speed SFP slots. The embedded Device Management System (DMS) provides the benefits of ease of use in the IP surveillance, wireless Access Point and other applications. The DMS capability built into the switches is new from Transition Networks and provides time-saving features enabling security integrators or network administrators to establish and document a baseline deployment, automatically discover and remotely configure attached IP-powered devices (PDs).

Features

- IPv6 Access Management
- Support Jumbo Frame up to 9K bytes
- Authentication – RADIUS, TACACS+
- DHCP Relay, DHCP Snooping, DHCP Server
- L2/L3/L4 ACLs Support MAC ACL, IP standard/extended ACL
- LLDP (Link Layer Discovery Protocol)
- IEEE 802.3az Energy Efficiency
- IP Source Guard, Port Security
- Syslog

PoE Features

- Compliant with IEEE 802.3at PoE+
- Compliant with IEEE 802.3af PoE
- PoE configuration
- Auto Power Reset (APR)

Specifications

Standards	IEEE 802.3 IEEE 802.3u IEEE 802.3z IEEE 802.3ae IEEE 802.3x IEEE 802.3ad IEEE 802.1D IEEE 802.1w IEEE 802.1s IEEE 802.1Q IEEE 802.1p IEEE 802.1ad IEEE 802.1AB IEEE 802.3af IEEE 802.3at
Connectors	(8) 10/100/1000 RJ-45 (2) 100/1000 SFP
Protocols	CSMA/CD
Technology	Store-and-Forward switching architecture
MAC Address	8K MAC address table
Backplane	20 Gbps
Dimensions	Width: 8.66" [220 mm] Depth: 9.53" [242 mm] Height: 1.73" [44 mm]
Power Input	100-240VAC
Power-over-Ethernet	Max PoE budget 130 Watts 30 Watts for (4) ports simultaneously 15.4 Watts for (8) ports simultaneously
Surge Protection	6KV
Environment	Operating: 0°C to +50°C Humidity: 10% to 90% (non-condensing)
Weight	4.4 lbs. [2.0 kg]
Compliance	FCC Class A, CE Safety: IEC60950
Warranty	Lifetime



Ordering Information

SM8TAT2SA

(8) 10/100/1000Base-T
+ (2) 100/1000 SFP Slots
(includes 19" rack mount brackets)

Power Cord Included

To order the corresponding country specific power cord, add the extension from the list below to the end of the SKU; Ex: SM8TAT2SA-NA

-NA = Country Code

-NA = North America
-LA = Latin America
-EU = Europe
-UK = United Kingdom
-SA = South Africa
-JP = Japan
-OZ = Australia
-BR = Brazil

Software Features

- Management: Web Management, SNMP V1/V2c/V3, Telnet, CLI
- Port Trunk: Supports IEEE 802.3ad port trunk with link aggregation control protocol (LACP) and static trunk.
- Multicast: Support IGMP Snooping V1/V2, MVR, MLD Snooping V1/V2
- Quality of Service: Supports 8 hardware queues. Strict priority and WRR, Ingress policer, Egress shaping and per port rate limiting
- Spanning Tree: Supports IEEE 802.1s MSTP, IEEE 802.1w RSTP and IEEE 802.1d STP Compliant
- VLAN: Port Based VLAN, IEEE 802.1Q tag-based, up to 4K VLAN entries, QinQ, MAC based VLAN, Private VLAN
- Firmware Update through TFTP and HTTP
- Device Management System (DMS)
 - Graphical Monitoring: Topology view, Floor view, Map View
 - Grouping, Batch update
 - Find my switch
 - Traffic Monitoring